



Dimensions (In.)

Specifications:

- Type: right angle DC power solder terminal
- Right angle application: 2.1mm (171-3215)
2.5mm (171-3216)
- Contact resistance: 50mΩ max.
- Insulation resistance: 100MΩ min.
- Breakdown voltage: 500VAC
- DC power & temperature rating: 12VDC 0.5A
- Color: black
- Contacts A, B, & terminal: nickel plated brass
- Insulator: ABS, UL94H-B
- Cap: PVC
- Operating temperature: -25°C ~ +70°C