



Dimensions (In.)

Electrical Specifications:

- Type: .56" dual digit
- Power dissipation: 120mW
- DC forward current: 20mA
- Reverse current: 100μA
- Operating and storage temperature: -45°C ~ 85°C
- Forward voltage: Hi-eff. red=2.2V (typ.) 2.8V (max.)
- Reverse current (Vr=5V): 100μA
- Peak emission wavelength @ (If=20mA): Hi-eff. red=655NM