



Dimensions (In.)

Mouser Stock No.	L (mH) ±10%	Q Min.	Test Freq. (kHz)	D.C.R. Max. (Ω)	Max. DC Current (mA)	SRF (MHz)
43LJ310	10.0	100	79.6	22	100	.30
43LJ312	12.0	100	79.6	23	100	.25
43LJ315	15.0	100	79.6	27	100	.20
43LJ318	18.0	60	79.6	34	100	.19
43LJ322	22.0	60	79.6	40	100	.18
43LJ327	27.0	60	79.6	47	100	.17
43LJ333	33.0	60	79.6	55	80	.16
43LJ339	39.0	35	79.6	60	80	.14
43LJ347	47.0	35	79.6	72	80	.13
43LJ356	56.0	35	79.6	110	50	.12
43LJ368	68.0	35	79.6	120	50	.11
43LJ382	82.0	35	79.6	150	50	.09
43LJ410	100.0	30	25.2	150	30	.08
43LJ412	120.0	30	25.2	200	30	.07
43LJ415	150.0	30	25.2	250	30	.06