

Antenna - ANT-DIR-5900-01 - 2701348

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Panel antenna, 5 GHz, 9 dBi, +/- 45° dual slant, apex angle h/v 70°/60°, 2* N (female), IP67



Product Features

- ✓ For transmission over larger distances

Key commercial data

Packing unit	0
Minimum order quantity	1
GTIN	 4 046356 739405
Custom tariff number	85177011
Country of origin	GERMANY

Technical data

General data

Frequency range	5 GHz
Frequency range	5.15 GHz ... 5.875 GHz
Horizontal beamwidth	70 ° (At 5 GHz)
Vertical beamwidth	60 ° (At 5 GHz)
Impedance	50 Ω
Gain	9 dBi
Connection method	N (female)
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Width	80 mm
Height	101 mm
Length	35 mm

Antenna - ANT-DIR-5900-01 - 2701348

Classifications

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC000416
ETIM 5.0	EC001698

UNSPSC

UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	20142601
UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215
eCl@ss 5.1	27242208
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208