




Dimensions: mm (in.)

SPECIFICATIONS	
Rating:	10A / 250VAC
Insulation Resistance:	500VDC 100M Ω Min.
Dielectric Strength:	1500VAC 1 minute
Fuse Size:	$\phi 5.2 \times 20L$ mm
Cap:	PBT
Contacts:	Copper alloy tin plated
RoHS Compliant by Exemption	