



Scotch® Vinyl Electrical Color Coding Tape 35-Yellow-1/2, 1/2 in x 20 ft (13 mm x 6,1 m), 100 per case

UPC# 00054007102571 3M Product Number 35-YELLOW-1/2 3M ID 80610833958



This yellow, 7 mil premium grade electrical vinyl tape stretches to conform to virtually any shape that requires color-coded insulation. Inner pack of 1 per sleeve, 10 per carton with 100 rolls per case.

Overview

Scotch® Vinyl Electrical Color Coding Tape 35 is used in phase identification, color coding leads and piping systems and for marking safety areas. This tape is abrasion- and weather-resistant, with excellent mechanical and electrical insulation properties.

Specifications

Adhesive Material	Rubber Resin
Agency Approvals	UL Listed; CSA; VDE 0340-TEIL1
Backing Material	Polyvinyl Chloride
Breaking Strength	17 Pound Per Inch (Of Width)
China RoHS - Below MCV	Yes
Color	Yellow
Dielectric Strength (V/mil)	1250 V/mil
EU RoHS Compliant	Yes
Length	20 Linear Foot
Maximum Operating Temperature (Celsius)	105 Degree Celsius
Operating Temperature Range	0 to 105 Degree Celsius
Operating Temperature Range (Fahrenheit)	32 to 220 Degree Fahrenheit
Product	Scotch® Vinyl Electrical Tape 35
Product Family	Scotch® Vinyl Color Coding Electrical Tape 35
Product Type	Vinyl Tape
Tape Color	Yellow
Tape Grade	Professional
Tape Length	20 Linear Foot
Tape Total Thickness	7 Milli-inch
Tape Total Thickness (metric)	0.177 mm
Tape Type	Vinyl Electrical
Tape Width	0.5 in
Thickness	7 Milli-inch (mil)
Width	1/2 Inch