



Dimensions: mm (in.)

SPECIFICATIONS	
Shaft hole:	1/4"
Insert:	Zinc
Material	Phenolic resin
Color:	Black
Indicator:	Painted, white dot
Tolerance:	$\pm 0.3\text{mm}$
RoHS compliant by exemption.	