



Dimensions: mm (in.)

SPECIFICATIONS	
Type:	control & instrument
Color:	black
Body material:	phenolic resin
Indicator:	painted white line
Shaft hole:	.25 inches
Tolerance:	$\pm 0.3$ mm
RoHS Compliant by Exemption	