


PART NUMBER (X SEE NOTE 5)	LENGTH (FEET)	TOLERANCE (INCHES)
73-779X-1	1	±0.25
73-779X-3	3	±1.00
73-779X-5	5	±1.50
73-779X-7	7	±2.00
73-779X-10	10	±2.00
73-779X-14	14	±3.00
73-779X-25	25	±4.00
73-779X-50	50	±12.00
73-779X-100	100	±18.00

DRAWING NO. 73-779X-1/100	
REVISIONS	
RELEASE FOR QUOTATION	
A	11-10-05



NOTES:

1. CABLES ARE DESIGNED WITH 50 MICRO-INCH GOLD-PLATED RJ45 MODULAR PLUG.
2. MOLDED CABLES HAVE A FLEXIBLE LOW-PROFILE SNAGLESS STRAIN RELIEF.
3. CAT5E CABLES ARE CONSTRUCTED OF UL 350 MHz 24 AWG UTP CABLE.
4. ALL CABLES ARE RETAIL PACKAGED WITH UPC-A BARCODE.
5. ETL TESTED & VERIFIED TO CATEGORY 5E STANDARD(EIA568B).
6. X= COLOR: 0-GRAY
1-BLACK
2-BLUE
3-GREEN
4-RED
5-YELLOW
6-WHITE
7-ORANGE
8-PINK
9-PURPLE

THIS DRAWING TO BE INTERPRETED
PER ANSI Y 14.5M - 1994

COMPANY CONFIDENTIAL

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY BETTY.YU		DATE 11-10-05	
DECIMALS	INCH	CHECKED BY BETTY.YU		DATE 11-10-05	
X	± 0.5	APPROVED BY THOMAS		DATE 11-10-05	
X.X	± 0.2				
X.XX	± 0.1				
ANGLES	± 0.5°	U/M		INCH	
THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.					
SHEET 1 OF 1		DRAWING NO. 73-779X-1/100		SIZE C	

EMERSON
Network Power
Connectivity Solutions
TITLE
C5E-350MHZ MOLDED