






NOTES:
1) RUBBER GASKET
2) ORDER PART #MJ-142

B MJ-142CP



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

A	NEW RELEASE	192	1/30 2014	HR
LET.	REVISION	CN #	DATE	CHK.

DWN.BY HR	DATE 1/30/14	MATERIAL		
CHECKED BY	DATE	FINISH		
APPR.BY	DATE	WEIGHT —	SCALE = 2.00 :1	NEXUS STAMFORD, CONN
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES &/OR (mm) TOLERANCES: DECIMAL: .XX[X.X] .XXX[X.XX] ± .0X[0.X] ± .00X[0.0X] FRACTION: X/X X/XX ± X/XX ANGLES: .X ± .X°		TITLE 2 CONDUCTOR JACK ASS'Y		
		DO NOT SCALE DWG.	SHEET 1 OF 1	
		SIZE B	DWG. NO. MJ-142CP	