

JKL LAMP PART NUMBER	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mArms)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF26188-20B	LCD HIGH OUTPUT WHITE 5600°k RGB	1000 @ 0°C	420	5	30,000 ± 10%	20,000

^{*} RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC	DIMENSIC IN MILLIM			IKI	COMPON	NENTS COD	DOD AT	ION
		\bigoplus	TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0						ION		
			THIRD ANGLE PROJECTION	2 PL +/- ANGLE +/-			FLU	ORESCENT L			
B	DIM CORRECT. AND 188+/-5.0 TO 188+/-3.0 STARTING & OPERATING VOLTAGE CHANGE		DRAWN BY L. WENGSTROM	APPV'D BY FD 10	DATE 0/17/00	SIZE	55335		26188-20B		
REV.	RELEASED DESCRIPTION/ECO NUMBER	3/13/00 APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE		RELEASED 3/13/98	REVISION DATE 10/17/00	NO. B	SHEET 1 OF 1	