



Dimensions: In.

SPECIFICATIONS	
Type:	Coax Cable Crimping Tool Kit with Storage/Carrying Case
Coax Stripper:	Strips RG 58/59/62/6/3C2V Cable
Die Tolerance:	±.003"
Die Material:	4140 Steel, HRC 42-50, Black Oxide Finish (A, B, & E), Natural Finish (C & D)
Crimping Tool Frame:	2.8mm Thick, Low Carbon Steel, HR30N 60-75, Black Oxide Finish
Cable Cutter Capacity:	ø.41" Max.
Cable Cutter Frame:	3.2mm Thick, Middle Carbon Steel, HRC 44-55, Black Oxide Finish

Die	Sizes	For RG Cable Types
A	.255, .213, .187, .068	55, 58, 59, 62, 140, 141, 142, 210, 223, 174, 303, 400, Fiber Optic, BELDEN 8279
B	.319, .256, .213, .068	6, 59, 62, 140, 210, BELDEN 8279, 55, 58, 141, 142, 223, 303, 400, Fiber Optic
C	.255, .213, .137, .100, .069, .043	59, 62, 8X, 140, 210, BELDEN 8279, 55, 58, 141, 142, 174, 223, 303, 400, Fiber Optic
D	.178, .151, .128, .078, .068, .042	122, 174, 179, 180, 187, 188, 195, Fiber Optic, 178, 316, BELDEN 8218
E	.429, .128, .100	8, 9, 11, 87A, 149, 165, 213, 214, 216, 225, 393, 174, 179, 187, 188, 316, BELDEN 9913