



Dimensions: in. (mm)

- Molded in tough and resilient natural colored Nylon 6/6 plastic.
- Spacers fit a variety of tube diameters from 3/4" dia. to 1-1/8" dia., and have inside diameters from .218" to .375" for attachment screws.
- Coved spacers are used for attaching parts to rods, tubes or curved contours.

SPECIFICATIONS				
Mouser Num.	Tube Dia. (ref)	A in. (mm)	B	L
561-130001	.75	.75 (19.05)	.26	.125
561-130002	.875	.843 (21.41)	.257	.156
561-130003	1	.835 (21.21)	.218	.5
561-130004	1	1 (25.4)	.26	.25
561-130005	1	1 (25.4)	.325	.25
561-130006	1.1	1 (25.4)	.25	.125
561-130007	1.125	.875 (22.23)	.375	.25