



Dimensions: mm (in.)

SPECIFICATIONS	
Wire:	AWG #24 Black and red 150mm ± 5mm Strip and tin 4mm ± 1mm
Material:	PP Resin, black color
Spring:	1.0mm 65C spring wire
RoHS Compliant	