




DIMENSIONS: in.

Nylon Locking Hole Plugs are available in a large selection of sizes from 3/16" to 2 1/2". These hole plugs are designed with multiple locks to positively snap in panel thicknesses ranging from 1/64" to 1/8". Locking Hole Plugs are used to close excess chassis holes, wiring outlets, and production access holes. These hole plugs are molded of heat stabilized nylon, and may be more suitable for critical or elevated temperature applications. Vent Plugs are available in the 3/4", 7/8" and 1" diameters. Locking Hole Plugs are stocked in black.

† Color - White

Mouser Stock Number	Dimensions: in.			
	Hole Diameter (A)	Head Diameter (B)	Thickness (C)	Max. Thickness
561-M2600	0.187	0.250±.015	0.234±.015	0.062
561-M2603	0.250	0.312±.015	0.312±.015	0.062
† 561-M2603W	0.250	0.312±.015	0.312±.015	0.062
561-62MP0312	0.312	0.375±.015	0.312±.015	0.062
† 561-62MP0312W	0.312	0.375±.015	0.312±.015	0.062
561-M2617	0.375	0.468±.015	0.406±.015	0.125
† 561-M2617-WT	0.375	0.468±.015	0.406±.015	0.125
561-M0437	0.437	0.531±.015	0.406±.015	0.125
561-M2643	0.500	0.578±.015	0.406±.015	0.125
† 561-M2643W	0.500	0.578±.015	0.406±.015	0.125
561-M2653	0.562	0.656±.015	0.406±.015	0.125
561-M2663	0.625	0.718±.015	0.406±.015	0.125
† 561-M2663W	0.625	0.718±.015	0.406±.015	0.125
561-M2683	0.750	0.922±.015	0.406±.015	0.125
† 561-M2683-WH	0.750	0.922±.015	0.406±.015	0.125
561-M2703	0.875	1.016±.015	0.453±.015	0.125
† 561-M2703W	0.875	1.016±.015	0.453±.015	0.125
561-M2713	1.000	1.203±.015	0.453±.015	0.125
561-MP1500	1.500	1.672±.015	0.453±.015	0.125
561-MP1750	1.750	1.925±.015	0.453±.015	0.125
561-MP2000	2.000	2.140±.015	0.453±.015	0.125
† 561-62MP0187W	0.187	0.250±.015	0.234±.015	0.062
RoHS Compliant				