



Dimensions: mm (in.)

SPECIFICATIONS

- Rating: 10A/250VAC
- Insulation Resistance: 500VDC 100M Ω Min.
- Dielectric Strength: 1000VAC 1 min.
- Fuse Type: $\phi 6.3 \times 30$ mm; 6.35×32 mm
- Cap and Frame: POM-F2003
- Terminal: Brass
- Wire: 16AWG UL1015
- Tolerance: ± 0.3 unless otherwise noted
- RoHS Compliant

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

EPD-200780