

$\frac{13}{16}$ "-UNEF28

**Material and Finish**

Body: PBT+30% Glass Filled,  
UL 94V-0 Rated, Black Color

IP Degree of Protection: IP67 when  
mated with GM67X-CBL-xxx-P or  
GM67X-S-88 and Gasket from  
GM67X-CS-B or GM67X-CS-R


| Tolerances                 |
|----------------------------|
| X.X ± 0.25                 |
| X.XX ± 0.10                |
| Unless Stated<br>Otherwise |

**RoHS COMPLIANT**  
EU Directive 2002/95/EC

| REV. | DATE    | DESCRIPTION     | REV. BY     | CHK. BY | DRAWN BY    | DATE   |
|------|---------|-----------------|-------------|---------|-------------|--------|
| A0   | 8/12/11 | New Drawing     | P. DalCanto | H. MA   | P. DalCanto | 5/5/11 |
| A1   | 8/30/11 | Release Drawing | P. DalCanto | N/A     |             |        |
|      |         |                 |             |         |             |        |
|      |         |                 |             |         |             |        |
|      |         |                 |             |         |             |        |
|      |         |                 |             |         |             |        |

**GM67X-CAP**

IP67 Modular Jack Cap



UNITS  
mm

