

Antenna cable - RAD-PIG-RSMA/N-1 - 2903264

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Antenna cable, 1 m in length; N (male) -> RSMA (male), impedance 50 ohms



The illustration shows a version of the product

Product description

Coaxial antenna adapter cable, N (male) to RSMA (male), 50 Ω, 1.0 m

Key commercial data

Packing unit	0
Minimum order quantity	10
GTIN	 4 046356 743679
Custom tariff number	85442000
Country of origin	UNITED STATES

Technical data

General

Connection method	RSMA (male)
Connection method	N (male)
Fixed cable length	1 m
Cable type	195
Cable, attenuation	0.55 dB @ 915 MHz
Cable, attenuation	0.80 dB @ 2.44 GHz
Cable, attenuation	1.10 dB @ 5.80 GHz
Minimum bending radius	12.70 mm
External diameter	4.95 mm
Connection method	RSMA (male)
Ambient temperature (operation)	-40 °C ... 85 °C

Classifications

ETIM

ETIM 3.0	EC001423
----------	----------

Antenna cable - RAD-PIG-RSMA/N-1 - 2903264

Classifications

ETIM

ETIM 4.0	EC000019
ETIM 5.0	EC001682

UNSPSC

UNSPSC 11	39121008
UNSPSC 12.01	43223108
UNSPSC 13.2	43223108
UNSPSC 6.01	30211506
UNSPSC 7.0901	43223108

eCl@ss

eCl@ss 4.0	27230207
eCl@ss 4.1	27250312
eCl@ss 5.0	27242208
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208