



Dimensions: mm (in.)

SPECIFICATIONS	
Wire:	AWG # 26 Black and red 150mm ± 5mm Strip and tin 5mm ± 1mm
Material:	PP Resin, black color
Spring:	0.6mm 65C steel nickel plated wire
RoHS Compliant	