



Dimensions: In.

SPECIFICATIONS	
Type:	shielded RF
Nominal impedance:	75Ω
Nominal capacitance:	68.5pF/m
Termination:	hi-rel BNC plug to RCA phono plug (172-2130) standard BNC plug to RCA phono plug (172-6670)
Cable type:	RG 59U
Cable size:	(1/0.65 x 1C + AC + 32/.12) x 1C OD=6.5mm
Conductor:	ø.65mm, copper clad steel
Conductor insulation:	low density polyethylene
Shield:	32/0.12mm OFC, aluminum braid
Jacket:	PVC, black
Jacket temperature rate:	80°C

Date Last Revised: 4-6-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300359

172-2130, 172-6670