



Circuit Diagram

DIMENSIONS: In.
(except where noted)

SPECIFICATIONS	
Type:	3.5mm chassis mount mono phone w/N/C switch
Contact resistance:	30mΩ max.
Insulation resistance:	100MΩ @ 500VDC
Dielectric withstand voltage:	500VAC for 1 minute
Housing:	polyoxymethylene
Bushing:	nickel plated brass
Break and earth terminals:	silver plated brass
Tip spring:	silver plated phosphor bronze