

**KOBICONN** 





Dimensions: mm (In)

SPECIFICATIONS	
Type:	Locking DC Power
Power Rating:	1A/12VDC
Insulation Resistance:	100MΩ min. @ 500VDC
Contact Resistance:	50mΩ max.
Voltage Breakdown:	500VAC for 1 Minute
Сар:	ABS Plastic
Inner Insulator:	Ebonite
Top Insulator:	Duracon
Body, Pin:	Nickel Plated Brass

Date Last Revised: 4-14-05

Available from Mouser Electronics 1-800-346-6873 www.mouser.com

KC-300465