







Phone Jack

161-3504

KOBI CONN

Phone Jack



Dimensions: In.

SPECIFICATIONS

Type:	PCB Mount, Hi-Rel, 2-SPST, N/C Switch
Contact Resistance:	30mΩ max.
Insulation Resistance:	50MΩ min. @ 100VDC
Withstand Voltage:	250VAC for 1 Minute
Operating Temperature:	-10°C ~ +70°C
Flammability:	230°C (3 Seconds)
Housing:	Noryl
Bushing:	Nickel Plated Brass
Terminals:	Nickel Plated Phosphor Bronze
Mounting Hole:	.250"

Date Last Revised: 10-15-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300484

161-3504