

## 3.55mm Jack 16PJ108





Tolerance ± 0.3 (w/o Indication)			
1	Contact A	1	Silver Plated
2	Contact B	1	Silver Plated
3	Contact C	1	Silver Plated
4	Case	1	Polycarbonate
5	Sleeve	1	Nickel Plated
6	Terminal	1	Silver Plated

Foot Print (Bottom View)



## **DIMENSIONS (IN.)**

SPECIFICATIONS			
Contact Resistance:	30mΩ max.		
Insulation Resistance:	50MΩ @ 100VDC		
Breakdown Voltage:	250VAC for 1 minute		
Life Cycle:	5000 Insertions		

Date Last Revised: 5-15-05

Available from Mouser Electronics 1-800-346-6873 www.mouser.com

KC-300488