




1/4" Mono Phone Jack

16PJ022



1/4" Mono Phone Jack



Circuit Diagram

Dimensions: In.

SPECIFICATIONS	
Type:	1/4" mono phone
Contact resistance:	30mΩ max
Insulation resistance:	50MΩ min @ 500VDC
Insulation withstand voltage:	60 seconds @ 500VAC
Insertion force:	2.5Kg max
Bushing, spring & contacts:	brass
Plating:	nickel
Insulator:	Duracon

Date Last Revised: 10-15-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300499

16PJ022