


PLCC Sockets

151-1530, 151-1546, 151-1570, 151-1586

KOBI CONN

PLCC Sockets



Dimensions: In.

SPECIFICATIONS

Type:	Surface Mount PLCC
Contact Resistance:	30mΩ max. @ 100mA DC
Insulation Resistance:	1000MΩ min. @ 500VDC
Current Rating:	1A
Voltage Rating:	500VAC for 1 Minute
Operating Temperature:	-65°C ~ +125°C

MATERIALS

Solder Pads:	.03" x .075"
Contacts:	Tin Plated Phosphor Bronze
Housing:	PPS & 40% Glass Fiber

MOUSER STOCK NO.	No. of Contacts	Dimensions: In.		
		A	B	C
151-1530	28	.30	.709	.771
151-1546	44	.50	.928	1.09
151-1570	68	.80	1.25	1.51
151-1586	84	1	1.42	1.76

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300748

151-1530, 151-1546, 151-1570, 151-1586