


Headers

151-23149, 151-23169

KOBI CONN

Headers



Dimensions: mm (In.)

SPECIFICATIONS

Type:	DIP through Pin
Contact Rating:	1A DC max.
Contact Resistance:	10mΩ max.
Insulation Resistance:	10MΩ min. @ 100VDC
Dielectric Strength:	1000VAC min. for 1 Minute
Capacitance Between Adjacent Pin:	.9pF max.
Operating Temperature:	-55°C ~ +125°C
Life:	100 Cycles min.
Solderability:	230°±5°C for 5±.5 sec., 95% Coverage

MATERIALS

Pins: Gold Plated

MOUSER STOCK NO.	Dimensions: mm (In.)		
	A	B	C
151-23149	17.70 (.697)	15.24 (.609)	10.1 (.398)
151-23169	20.30 (.799)	17.78 (.711)	10.1 (.398)

Date Last Revised: 3-15-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300750

151-23149, 151-23169