


Terminal Blocks

158-P02ESK508V2, 158-P02ESK508V3



Terminal Blocks

158-P02ESK508V2, 158-P02ESK508V3



PCB Layout

P	02P	03P
U	5.08	10.16
V	10.16	15.24

Dimensions: mm (In.)

MATERIAL SPECIFICATIONS

Solder pin:	Copper, Tin plated
Screw:	Steel, Zinc plated
Wire cage:	Steel, Zinc plated
Housing:	PA66, Green

ELECTRICAL SPECIFICATIONS

Rating:	600V 23A
Pitch:	5.08 mm
Insulation withstand voltage:	1500V/Min.
Insulation resistance:	300MΩ or more at DC500V
Temperature range:	-40°C~+105°C
Screw torque value:	8kgf-cm (Max)
Electric wire:	AWG 26~12

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300764