


Terminal

158-P02EK508A2, 158-P02EK508A3

KOBI CONN

Terminal



Dimensions mm (In.)

ELECTRICAL SPECIFICATIONS

Rating:	300V 20A
Pitch:	5.08mm
Insulation withstand voltage:	AC 2000V/Min
Insulation resistance:	500MΩ or more at DC500V
Temperature range:	-40°C~+105°C
Screw torque value:	4kg-cm
Electric wire:	AWG 24~12

MATERIAL SPECIFICATIONS

Screw:	Steel, Zinc Plated
Wire cage:	Steel, Zinc Plated
Solder pin:	Copper, Solder Plated
Housing:	PA66 Green

Date Last Revised: 10/19/05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300807

158-P02EK508A2, 158-P02EK508A3