

163-2307-E



SPECIFICATIONS	
Plastic Housing:	LCP, black
Operating Temperature:	-25°C to +85°C
Insertion & Extraction Force:	0.2Kgs to 2.0Kgs
Contact Resistance:	50mΩ max.
Insulation Resistance:	100MΩ (min.)
Withstand Voltage Test:	250VAC 50 to 60Hz for 1 min.
Center Pin:	nickel plated brass
Rated Voltage:	4-20VDC
Rated Current:	3.0A
Contacts:	tin plated brass
Durability Test:	5000 mating cycles
RoHS Compliant	

KC-300982

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.