


UK Socket

161-RB0200-E

KOBICONN

UK Socket



Dimensions: mm (in.)

SPECIFICATIONS

Insulation Resistance:	Over 100MΩ at 500V DC
Dielectric Strength:	2000V AC 1 Minute
Body Material:	Thermoplastic
Standard:	BS-1363-2

RoHS Compliant

Date Last Revised: 6-29-12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301219

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-RB0200-E