



DC Power Jack SMT

163-17921-EX

KOBI CONN

DC Power Jack SMT



DIMENSIONS: mm

ELECTRICAL SPECIFICATIONS

Rating:	DC12V 1A
Contact Resistance:	50mΩ max.
Insulation Resistance:	100MΩ at 500V DC
Withstand Voltage:	AC 500V for 1 minute
Operation Force:	Refer attach specification
Switching Life:	5K cycles min

MATERIAL SPECIFICATIONS

No.	Description	Qty.	Material
1	Frame	1	Nylon 46
2	Cover Board	1	Nylon 46
3	Terminal	1	Brass
4	Spring Plate	2	CuBe
5	Terminal	1	Brass
6	Center Pin	1	Copper Alloy
RoHS by Exemption			

Date Last Revised: 03/26/13

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301435

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

163-17921-EX