



Last Update: 12-01-05 **Ref.** #: MS-100617

Dimensions: mm (In.)









Electrical Specifications:

- Rating: 50mA/12VDC
- Contact resistance: 100mΩ max.
- Insulation resistance: 100MΩ min. @ 500VDC
- Dielectric strength: 250VAC for 1 minute
- Life: 500,000 cycles

Mechanical Specifications:

- Type: SPST
- Operating force: 160±50gf
- Stroke: .25mm +.2mm -.1mm
- Operating temperature: -25°~+70°C

Note:

 RoHS Compliant and process compatible with 260° solder

Material:

Button color: brown

Tactile Switch (Thru-Hole) 101-0661-EV



Available from Mouser Electronics

www.mouser.com

1-800-346-6873