
Last Update: 4/24/08 **Ref.** #: MS-101214

Dimensions: mm (in.)



Electrical Specifications:

- Contact Rating: 1mA/10VDC
- Contact Resistance: ≤ 10Ω
- Insulation Resistance: ≥ 50MΩ 50V DC
- Dielectric Strength: 50V AC 1 minute

Mechanical Specifications:

- Operating Force: 25± 10gf
- Operating Temperature: -10°C ~ +60°C
- Number and Postions of Segment Points: 12 Segment points (each segment angle: 30°±3°)
- Output Resolution: 6 pulse/360°

Note:

RoHS Compliant

Encoder 101-5413-EV

