





COMMENT: ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT, THIS DRAWING IS NOT TO BE REPRODUCED, COPIED, TRANSMITTED OR OTHERWISE DISCLOSED TO A THIRD PARTY. AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +130°C)	black
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

		Measurement without tolerance acc. to ISO 2768-m SCALE 2:1		TITLE D-Sub Mixed-Layout Connector		
		NAME / DATE				
		DRAWN Denzinger 16-05-2003				
		CHECKED Floßmann 16-05-2003				
				DWG.NO. F2W2PC-K120		
				REV. 1		
1	REV.	DATE	CH.-NO.	ORIGINAL: DIN A3-DRAWING AS A FILE	REPLACEMENT FOR: F2W2PC-K120 a	PAGES 1