



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234

Model Number: SU6000RT4UHV

SmartOnline 6kVA On-Line Double-Conversion UPS, 4U Rack/Tower, 200-240V C19 outlets

Highlights



- 6kVA / 6000VA / 5400W on-line double-conversion UPS; 0.9 power factor
- 200/208/220/230/240V 50/60Hz output; High efficiency economy mode option
- 4U Rack/Tower compatible; Hot-swap power and battery modules
- USB, RS232 & EPO ports; SNMP/WEB and contact-closure card options
- Front panel LEDs with detailed LCD monitoring and control screen
- Expandable runtime with optional external battery packs
- Hardwire input (3 wire) with optional cordsets available; C19 outlets

Description

Tripp Lite SU6000RT4UHV 6000VA / 6kVA / 5400 watt on-line, double-conversion UPS system offers complete power protection for critical server, network and telecommunications equipment in a single 4U rack/tower compatible housing. Full-time active power conditioning provides clean, continuous dual-conversion AC output free of voltage fluctuations, power interruptions and line noise. Fault-tolerant auto-bypass prevents unexpected service interruptions during UPS overload or internal fault conditions. Detachable back panel PDU with manual bypass switch supports hot-swappable whole UPS replacement with no interruption to connected equipment. Single all-in-one rack / tower housing installs in only 4 rack spaces (4U) with a maximum installed depth of only 20.7 in. / 52.6cm. Maintains full-time sine wave output within 2% of selectable 200/208/220/230/240V nominal during brownouts as low 100V and overvoltages as high as 300V. Expandable runtime is supported with optional BP192V12-3U external battery packs. Battery independent restart ensures automatic UPS power-up without user interaction after lengthy power outages, even when batteries are expired and require replacement. Double-conversion operation converts raw input from AC to DC, then re-synthesizes output power back to perfect sine wave AC with enhanced protection from harmonic distortion, fast electrical impulses and other hard-to-solve power problems not addressed by other UPS types. Highly efficient operation in optional economy mode significantly reduces BTU heat output and operating energy costs. Network-grade AC surge and noise suppression. Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via built-in RS-232 and USB interfaces. Optional SNMP/Web and contact-closure communications card accessories available. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Included PowerAlert monitoring software offers detailed site power and UPS updates with support for safe auto-shutdown of connected systems as UPS batteries become depleted. Included software packages include PowerAlert Local, PowerAlert Network Shutdown Agent and PowerAlert Network Management System for complete support for a wide variety of application types. Supports Emergency Power Off (EPO) via built-in interface. Front panel LEDs and LCD readout with scroll controls support front-panel visual monitoring of all major UPS for a variety of control options to support advanced UPS settings and configurations. LED / LCD display panel rotates for viewing in rackmount or tower configurations. Hardwire input and 4 C19 outlets. Support for optional North American and International cordsets. External battery packs are field replaceable and hot swappable.

Package Includes

- SU6000RT4UHVP Hot-swappable UPS Power Module
- SUPDMB6KIEC Detachable PDU with Maintenance Bypass Switch
- PowerAlert Software CD
- 1 x 6-ft. USB Cable
- 1 x 6-ft. DB9 Cable
- 4-Post Rackmount Hardware

Features

- Tripp Lite SU6000RT4UHV 6000VA / 6kVA / 5400 watt on-line, double-conversion UPS system in a single 4U rack/tower compatible housing (output is limited to 4992 watts when used at 208V with L6-30P input plug)
- Full-time active power conditioning maintains clean, continuous dual-conversion AC output free of voltage fluctuations, power interruptions and line noise
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Detachable back panel PDU contains hardwire input line cord connection, output receptacles and manual bypass switch to support

hot-swappable whole UPS replacement with no interruption to connected equipment

- Hardwire input and 4 C19 output receptacles
- Included rail kit supports 4U 19 inch rackmount installation in 4 post racks
- Optional 2POSTRMKITHD supports installation in 2 post 19 inch racks (1 required for SU6000RT4UHVg)
- Optional 2-9USTAND supports upright tower placement (1 required for SU6000RT4UHVg)
- Maximum installed rack depth of only 20.7 in. / 52.6cm
- Maintains full-time sine wave output within 2% of selected 200/208/220/230/240V nominal in double conversion mode
- Corrects brownouts to 156V at full load (100V at 50% load or less)
- Corrects overvoltages to 290V at full load (300V at 90% load or less)
- Supports 50/60Hz operation for worldwide frequency compatibility
- Double-conversion operation offers full-time AC to DC, then DC to AC conversion to maintain perfectly regulated sine wave AC output with enhanced protection from harmonic distortion, fast electrical impulses and other hard-to-solve power problems not addressed by other UPS types
- High efficiency ECONOMY MODE operation significantly reduces BTU heat output and operating energy costs
- Network-grade AC surge and noise suppression
- Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via built-in RS-232, USB and optional SNMP card slot interfaces
- UPS card slot supports one card-based network interface option (part # SNMPWEBCARD) or dry-contact monitoring accessory (part # RELAYIOCARD)
- Optional SNMPWEBCARD offers communications and control via secure remote web and network interfaces
- Optional RELAYIOCARD supports six configurable hard contact closure outputs for custom event notification
- Optional RELAYIOMINI interface module offers three configurable hard contact closure outputs for custom event notification (requires removal of USB interface module)
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Includes Free PowerAlert monitoring software packages; PowerAlert LOCAL for desktops and small business networks, PowerAlert NSA (Network Shutdown Agent) for larger networks and PowerAlert NMS (Network Management System) for monitoring up to 250 SNMP-enabled UPS, PDU and other networking devices
- Front panel LEDs and LCD readout with scroll controls support front-panel visual monitoring of all major UPS functions with support for a variety of control options to support advanced UPS settings and configurations
- LED/LCD display panel rotates for viewing in rackmount or tower configurations
- Supports Emergency Power Off (EPO) via built-in interface
- Battery independent restart ensures automatic UPS power-up without user interaction after lengthy power outages, even when batteries are expired and require replacement
- BP192V12-3U external battery packs are field replaceable and hot swappable
- Some external battery configurations require the use of Tripp Lite's [External Battery Configuration Software](#) (see manual)
- Frequency conversion mode enables conversion of 60Hz to 50Hz or 50Hz to 60Hz (no de-rating)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	6000
Output kVA capacity (kVA)	6.0
Output Watt Capacity (watts)	5400
Output kW capacity	5.4
Output power factor	0.9
Output Capacity Details	Output capacity de-rates to 4992 watts when used at 208V with optional L6-30P line cord
Crest Factor	3:1
Nominal Output Voltage(s) Supported	200V; 208V; 220V; 230V; 240V

Frequency compatibility	50 / 60 Hz
Frequency compatibility details	Output frequency matches input nominal on startup; Frequency conversion mode enable conversion of 60Hz to 50Hz or 50Hz to 60Hz (no de-rating)
Output voltage regulation (line mode)	+/- 2%
Output voltage regulation (Economy line mode)	+/- 10%
Output voltage regulation (Battery mode)	+/- 2%
Built-in UPS output receptacles	4 C19 outlet(s)
Output receptacle details	Output receptacle and input connections are mounted on a detachable PDU backplate with bypass switch to enable hot-swappable power module replacement
Output circuit breaker	Two 20A breakers protect 2 C19 outlets each
Output AC waveform (AC mode)	Pure Sine wave
Output AC waveform (battery mode)	Pure Sine wave
INPUT	
Rated input current (at maximum load)	31.9A (200V), 30.6A (208V), 29A (220V), 27.7A (230V), 26.6A (240V)
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 220V AC; 230V AC; 240V AC
Nominal input voltage description	Factory configured to 208V
UPS input connection type	Hardwire
UPS input connection description	Optional SU30ACORD offers L6-30P input cable
Recommended Electrical Service	40A (200/208v); 30-32A (220/230/240v)
Phase	Single-Phase
BATTERY	
Full load runtime (minutes)	2 minutes (5400 watts)
Half load runtime (minutes)	8.5 minutes (2700 watts)
Expandable battery runtime	Runtime is expandable with external battery packs
External battery pack compatibility	BP192V12-3U; BP192V557C-1PH; BP192V787C-1PH; BP192V1037C-1PH; BP192V1407C-1PH
DC system voltage (VDC)	192

Battery recharge rate (included batteries)	6 hours from 10% to 90% (internal batteries)
Replacement battery cartridge (internal UPS battery replacement)	RBC5-192
Battery Access	Front panel battery access door
Battery replacement description	Hot-swappable, user replaceable internal batteries
VOLTAGE REGULATION	
Voltage regulation description	Online, double-conversion power conditioning
Overvoltage correction	Corrects overvoltages as high as 300V (
Undervoltage correction	Corrects undervoltages as low as 100 (
LEDS ALARMS & SWITCHES	
LED Indicators	6 LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status; LCD screen offers additional information and control options
Alarms	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
Alarm cancel operation	Alarm cancel switch
Switches	Includes main power off/on switch, plus 2 switches to set and execute scrollable LCD functions. A manual bypass switch featured on the detachable PDU allows for complete removal of the UPS during routine maintenance without disrupting power to connected loads.
SURGE / NOISE SUPPRESSION	
UPS AC suppression response time	Instantaneous
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with optional accessories	2 post rackmount (2POSTRMKITWM); Tower (2-9USTAND)
Primary form factor	Rackmount
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	6.85 x 17.5 x 20.7
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	17.4 x 44.5 x 52.6
Rack Height	4U
Secondary form factor	Tower
UPS / Power Module weight (lbs)	108

UPS / Power Module weight (kg)	49
UPS Shipping dimensions (height x width x depth / inches)	12.7 x 23.6 x 29.1
UPS Shipping dimensions (height x width x depth / cm)	32.3 x 59.9 x 73.9
Shipping weight (lbs)	156.5
Shipping weight (kg)	71.1
Cooling method	Fans
UPS housing material	Steel
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	1767
AC economy mode BTU / hr. (full load)	707
Battery mode BTU / hr. (full load)	1784
AC mode efficiency rating (100% load)	90%
AC economy mode efficiency rating (100% load)	96%
Operating Elevation (ft.)	0-3000m (0 to 10,000 ft.)
Audible Noise	60 dBA at front side 1 meter
Operating Elevation (m)	0-3000 m
COMMUNICATIONS	
Communications interface	USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	Additional contact closure support with optional RELAYIOCARD and RELAYIOMINI interface cards. RELAYIOMINI installation requires removal of panel containing USB ports
PowerAlert software	Included
Communications cable	USB, DB9 serial and EPO cables included
WatchDog compatibility	Yes
LINE / BATTERY TRANSFER	

Transfer time	No transfer time (0 ms.) in online, double-conversion mode
Transfer time (economy mode)	8 ms. typical power failure response in optional economy mode
Low voltage transfer to battery power (setpoint)	156V (full load) / 100V (50% load or less, derates linearly)
High voltage transfer to battery power (setpoint)	280V (full load) / 300V (90% load or less)
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Automatic inverter bypass; Manual bypass switch; Detachable hot-swap PDU; Hot swappable UPS power module; Hot swappable batteries
Green & high efficiency features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); CE; Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances)
UPS Certification details	IEC 61000-4-5 1995 B Surge Immunity
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
WEXT3-SU6000HV	3-Year Extended Warranty - For SU6000RT3UHV only	1
WEXT5-SU6000HV	5-Year Extended Warranty - For SU6000RT3UHV only	1
BP192V12-3U	BP192V12-3U - External Battery Pack for UPS System	1
SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
SU30ACORD	SU30ACORD - Optional Input Cord for UPS System	1
RELAYIOMINI	3 Relay I/O Mini-module	1
2POSTRMKITHD	Enables 2-Post Rackmount Installation of 3U and Larger UPS, Transformer and Battery Pack Components	1
2-9USTAND	Enables Tower Placement of Rackmount UPS Systems	1
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
RELAYIOCARD	Programmable Relay I/O Card	1

