

FOR REFERENCE ONLY

SPECIFICATIONS:

AC RATING: 10 AMPS @115VAC (RESISTIVE LOAD)
5 AMPS @115VAC (INDUCTIVE LOAD)
3 AMPS @115VAC (LAMP LOAD)

DC RATING: 10 AMPS @28VDC (RESISTIVE LOAD)
5 AMPS @28VDC (INDUCTIVE LOAD)
3 AMPS @28VDC (LAMP LOAD)

MECHANICAL LIFE: 500,000 CYCLES
ELECTICAL ENDURANCE: 20,000 CYCLES @ SEA LEVEL
5,000 CYCLES @ 50,000 FEET

ACTION: MOMENTARY SNAP

OPERATING FORCE:
SERIES 20 & 30: 3 TO 5 POUNDS MOMENTARY
1/2 TO 2 POUNDS PUSH-PULL
SERIES 22 & 32: 2 TO 3 POUNDS MOMENTARY

WEIGHT: .050 POUNDS MAXIMUM


CASE: ALUMINUM ALLOY 2011-T3,
"EU" (ROHS COMPLIANT)
CLEAR ANODIZED IAW MIL-A-8625

PLUNGER: GLASS FILLED NYLON

BODY: DIALLYL PHTHALATE IAW MIL-M-14

TERMINALS: THREADED #2-56 NC-2B


B NX223002B-XX




ORDERING INFORMATION:

NX223002B-00 SWITCH ONLY
NX223002B-60 SWITCH, MOUNTING HARDWARE
NX223002B-61 SWITCH, MOUNTING HARDWARE, TERNIMAL HARDWARE
NX223002B-00EU SWITCH (ROHS) ONLY
NX223002B-60EU SWITCH (ROHS), MOUNTING HARDWARE (ROHS)
NX223002B-61EU SWITCH (ROHS), MOUNTING HARDWARE (ROHS), TERNIMAL HARDWARE


THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.



TERMINAL
HARDWARE




SW-200-26
1/2-32 NUT
(1)




SW-200-27
1/2
LOCKWASHER
(1)

MOUNTING
HARDWARE



SW-200-26
1/2-32 NUT
(1)



SW-200-27EU
1/2 (ROHS)
LOCKWASHER
(1)

MOUNTING
HARDWARE
(ROHS)

A	INITIAL RELEASE		4/16/07	EWT
LET.	REVISION	CN #	DATE	CHK.

DWN. BY	EWT	DATE	4/16/07	MATERIAL	N/A
CHECKED BY		DATE		FINISH	N/A
APPR. BY		DATE		WEIGHT	—
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON				SCALE	N/A
.XX .XXX ANGLES				TITLE	SWITCH 2-CIRCUIT MOMENTARY 2LB
— ±.003 ±.5°				DO NOT SCALE DWG.	SHEET 1 OF 1
				SIZE	B
				DWG. NO.	NX223002B-XX

NEXUS
STAMFORD, CONN