




Dimensions: mm

Mouser Stock No.	A	B	C	D	E	F	G	H	Markings
450-CK1532	14.7	13.0	16.2	3.2	6.7	0.0	7.3	10.0	No Line
450-CK1560	14.7	13.0	16.2	6.0	6.7	0.0	7.3	10.0	No Line
450-CK1564	14.7	13.0	16.2	6.4	6.7	0.0	7.3	10.0	No Line
450-CKL560	14.7	13.0	16.2	6.0	6.7	0.0	7.3	10.0	White Line
450-CKL564	14.7	13.0	16.2	6.4	6.7	0.0	7.3	10.0	White Line
450-CK2160	21.3	19.6	17.1	6.0	10.0	3.2	5.0	17.0	No Line
450-CK2164	21.3	19.6	17.1	6.4	10.0	3.2	5.0	17.0	No Line

SPECIFICATIONS

Material:	Plastic
Tolerance:	± 0.20
Indicator:	3.2mm, 6mm, 6.4mm shaft