




DIMENSIONS: mm (in.)

SPECIFICATIONS

Rating:	10A/250VAC
Insulation Resistance:	500VDC 100M Ω Min.
Dielectric Strength:	1500VAC 1 Min.
Fuse Type:	$\phi 6.3 \times 30\text{mm}$; $6.35 \times 32\text{mm}$
Terminal:	Brass
Wire:	16AWG
Tolerance:	± 0.3 unless otherwise noted
RoHs Compliant	

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

EPD-200780