

IN-LINE GLASS FUSEHOLDERS

150322



Description

The 150322 is a 500 VAC/125 VDC rated inline fuseholder ideal for applications where supplemental protection is needed, such as lighting ballasts and power supplies. 8-inch pre-stripped wire leads and fuse clips come preassembled for quick installation.


Features/Benefits

- Single piece body minimizes component count
- High voltage rating accommodates many power applications
- Wire leads are pre-attached to fuse clips for quick assembly
- Single piece molded body
- UL Recognized

Recommended Fuses

3AG (312, 313 Series)
 3AB (314, 326, 505 Series)

Dimensions in mm (inches)



Specifications

Voltage Rating:	500 VAC, 125 VDC
Ampere Rating:	15 A
Fuse Type:	¼" x 1¼"
Fuse Clips:	Tin-plated brass
Wire:	Black 18 AWG, 150° C Stranded
Molded Body:	Single piece thermoplastic
Flammability Rating:	UL94 V-0
Approvals:	UL Recognized (File No. E14721)
Environmental:	RoHS complaint and Pb free
Storage Temperature:	-40° C to 80° C
Operating Temperature:	-55° C to 125° C

Ordering Information

CATALOG NUMBER	SYSTEM NUMBER	STANDARD PACK
150322	01500322H	100 PIECES

Web Resources

Sample requests, downloadable CAD drawings and other technical information: www.littelfuse.com/150322

Additional In-Line Glass Fuseholders

Twist-Lock

155 Series



In-Line Mount
 Low Voltage 3AG, SFE



Heavy-Duty Bayonet

155 Series



In-Line Mount
 Low Voltage 3AG



Special Type



150 Series



In-Line Mount
 2AG, 5x20mm



Dimensions in (inches)



Web Resources

For more information, visit: www.littelfuse.com/150
www.littelfuse.com/155