



FLASH PLUSCON

October 2010

M12 SAC Plastic

Further expanding our M12 sensor/actuator cable offering, we now introduce an M12 connector with a black polyamide (plastic) coupling nut.

- 3-, 4-, and 5-pole configurations
- Corrosion-resistant coupling nut
- PUR halogen-free cable
- IP65/IP68/IP69K



Order info:

Connector 1	Connector 2	Cable Length	Order No.		
			M12 – 3-Pole	M12 – 4 -Pole	M12 – 5-Pole
Male straight	Open end	1.5 m	1456006	1442353	1442395
Male straight	Open end	3 m	1442324	1442366	1442405
Male straight	Open end	5 m	1442337	1442379	1442418
Male straight	Open end	10 m	1442340	1442382	1442421
Male angled	Open end	1.5 m	1442557	1442599	1442638
Male angled	Open end	3 m	1442560	1442609	1442641
Male angled	Open end	5 m	1442573	1442612	1442654
Male angled	Open end	10 m	1442586	1442625	1442667
Female straight	Open end	1.5 m	1442434	1442476	1442515
Female straight	Open end	3 m	1442447	1442489	1442528
Female straight	Open end	5 m	1442450	1442492	1442531
Female straight	Open end	10 m	1442463	1442502	1442544
Male straight	Female straight	0.3 m	1442793	1442832	1442874
Male straight	Female straight	0.6 m	1442803	1442845	1442887
Male straight	Female straight	1.5 m	1442816	1442858	1442890
Male straight	Female straight	3 m	1442829	1442861	1442900
Female angled	Open end	1.5 m	1442670	1442719	1442751
Female angled	Open end	3 m	1442683	1442722	1442764
Female angled	Open end	5 m	1442696	1442735	1442777
Female angled	Open end	10 m	1442706	1442748	1442780