

Main

Range of product	Zelio Relay
Product or component type	Socket
Contact terminal arrangement	Mixed
Product compatibility	Relay RXM2.... Relay RXM4....
Device short name	RXZ
Sale per indivisible quantity	10

Complementary


[Ith] conventional free air thermal current	10 A
[Ue] rated operational voltage	< 250 V
Tightening torque	<= 1 N.m (M3 screw(s))
Fixing mode	By screw mounting on panel Clip-on mounting on 35 mm symmetrical DIN rail
Marking	CE
Width	27 mm
Product weight	0.056 kg

Environment

Connections - terminals	Connector, flexible cable with cable end 1 x 0.25...1 x 2.5 mm ² /AWG22...AWG14 Connector, flexible cable with cable end 2 x 0.25...2 x 1 mm ² /AWG22...AWG17 Connector, solid cable without cable end 1 x 0.5...1 x 2.5 mm ² /AWG20...AWG14 Connector, solid cable without cable end 2 x 0.5...2 x 1.5 mm ² /AWG20...AWG16
Standards	IEC 61984
Product certifications	CSA UL
Ambient air temperature for storage	-40...85 °C
Ambient air temperature for operation	-40...55 °C
IP degree of protection	IP20 conforming to EN/IEC 60529
Dielectric strength	2500 V
RoHS EUR status	Compliant
RoHS EUR conformity date	0801

Socket

Socket with Mixed Contact Terminals and Connector



- 1 Relay
- 2 Protection Module
- 3 Carriage Stirrup