

**Technical Characteristics**

Ampere Rating	6A
Degree of Protection	IP20
External Control Voltage	24VDC
Horsepower Rating	1.0 to 1.5HP@230VAC - 2 to 3HP@460VAC
Input Voltage	200-480VAC
Type	ATS01
Soft Starting Time	1 to 10 seconds (adjustable)
Soft Stopping Time	1 to 10 seconds (adjustable)
Depth	5.31 inches
Marketing Trade Name	Altistart 01
Number of Functions	1
Input Phase	3-Phase
Height	4.88 inches
Width	1.77 inches
Output Phase	3-Phase

Shipping and Ordering

Category	22392 -
Discount Schedule	I11
Article Number	785901923343
Package Quantity	1
Weight	0.93 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.