

Product data sheet

Characteristics

8501KPD13V53

RELAY 240VAC 6.6AMP TYPE K +OPTIONS



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility



Main

Commercial Status	Commercialised
Range of product	8501K
Product or component type	Relay
Contacts material	Silver tin oxide
Switch function	3PDT
Control circuit voltage	24 V DC
Rated power in hp	0.5 hp 240 V 0.33 hp 120 V
Maximum switching voltage	240 V AC
Mounting support	Socket
Ambient air temperature for operation	-40...158 °F
Shape of pin	Tubular
Product certifications	CE CSA RoHS UL recognized
Operating time	18 ms pick-up 7 ms drop-out
Local signalling	No indicator
Control type	Without
Product compatibility	8501NR61 8501NR62
Relay type	General purpose

Ordering and shipping details

Category	21141 - 8501 KP
Discount Schedule	CP2
GTIN	00785901480488
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CN

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0702 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------