

Product data sheet

Characteristics

8501KU12V20

RELAY 240VAC 12AMP TYPE K +OPTIONS



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility



Main

Commercial Status	Commercialised
Range of product	8501K
Product or component type	Relay
Contacts material	Silver tin oxide
Switch function	DPDT
Control circuit voltage	120 V AC
Rated power in hp	0.5 hp 240 V 0.33 hp 120 V
Maximum switching voltage	240 V AC
Mounting support	Socket
Ambient air temperature for operation	-40...131 °F
Shape of pin	Spade
Product certifications	CE CSA RoHS UL recognized
Operating time	8 ms drop-out 8 ms pick-up
Local signalling	No indicator
Control type	Without
Product compatibility	8501NR82
Relay type	General purpose

Ordering and shipping details

Category	21144 - 8501 KU
Discount Schedule	CP2
GTIN	00785901480853
Nbr. of units in pkg.	1
Package weight(Lbs)	0.19
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CN

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0702 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------