

8501NR34

RELAY SOCKET 300VAC 10A TYPE R +OPTION



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

NATO products



Main

Commercial Status	Commercialised
Range of product	8501N
Product or component type	Relay Socket
[In] rated current	10 A
Product certifications	CE CSA RoHS UL recognized
Shape of pin	Spade
Pin number	14
Mounting support	DIN rail Panel
Quantity per set	Set of 1
Electrical connection	Double tiered screw clamp terminals

Ordering and shipping details

Category	21142 - 8501 N
Discount Schedule	CP2
GTIN	00785901137313
Nbr. of units in pkg.	1
Package weight(Lbs)	0.17
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CN

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0639 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.