

Main

Ampere Rating	15A
Application	Suited for use as logic elements and power switching output devices.
Approvals	UL Recognized File Number: E78351 CCN: NLDX2 - CSA Certified File Number 211268 Class 321107 - CE Marked - UL Listed File Number: E78351 CCN: NLDX
Coil Voltage	24VDC
Contact Arrangement	SPDT
Contact Material	Silver Cadmium Oxide
Contact Rating	240VAC/28VDC
Maximum Voltage Rating	28VDC
Mounting Type	Socket
Number of Pins	5 Pin
Number of Poles	1-Pole
Operating Temperature Range	-40 to 158 Degrees F
Operating Times	Pick-Up: 20ms - Drop-Out: 20ms
Phase	1-Phase
Type	R
Type of Pins	Spade