



Product availability: Stock - Normally stocked in distribution facility

NATO products



Main

Commercial Status	Commercialised
Range of product	9050JCK
Product or component type	Timer
[In] rated current	10 A
Switch function	DPDT
Contacts type and composition	2 NO + 2 NC
Control circuit voltage	24 V AC/DC
Maximum switching voltage	240 V AC
Mounting support	Socket
Pin number	8
Shape of pin	Tubular
Product certifications	CE CSA UL listed
Time delay type	On-delay
Time delay range	0.1...10 s

Ordering and shipping details

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
GTIN	00785901032687
Nbr. of units in pkg.	1
Package weight(Lbs)	0.24
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0627 - Schneider Electric declaration of conformity

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.