

Main

Ampere Rating	10A
Application	Designed for multipole switching applications at 240 volts or lower
Approvals	UL Listed File Number E197072 CCN NRNT2 - CSA Certified File Number 212845 Class 321107 - CE Marked
Coil Voltage	120VAC@50/60Hz
Contact Arrangement	DPDT
Contact Material	Silver Nickel
Contact Rating	240VAC/28VDC
Depth	2.66 Inches
Height	1.39 Inches
Horsepower Rating	1/3HP@120VAC - 1/2HP@240VAC
Maximum Voltage Rating	240VAC
Mounting Type	Socket
Number of Pins	8 Pin
Number of Poles	2-Pole
Operating Temperature Range	-40 to 131 Degrees F
Operating Times	Pick-Up: 12ms - Drop-Out: 12ms
Phase	1-Phase
Pilot Light	Yes
Type	KP
Type of Pins	Tubular
Width	1.39 Inches

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.