



List Price \$52.00 USD

Availability **Stock Item:** This item is normally stocked in our distribution facility.

Technical Characteristics

Approvals	UL Listed File Number E78351 CCN NLDX - CSA Certified File Number 214768 Class 321107 - CE Marked
Catalog Reference Number	9050CT9601
Ampere Rating	10A
Horsepower Rating	1/3HP@120VAC - 1/2HP@240VAC
Type	JCK
Type of Pins	Tubular
Timing Mode	On Delay
Timing Range	0.1 - 10 Seconds
Contact Break	3A@120VAC, 1.5A@240VAC
Mounting Type	Socket
Maximum Voltage Rating	240VAC
Number of Pins	8 Pin
Contact Make	30A@120VAC, 15A@240VAC
Contact Configuration	2 N.O./2 N.C.
Contact Arrangement	DPDT
Features	Up to +/- 0.1 Percentage Repeat Accuracy; Transient Protected; Variable or Fixed Time Delay; Available in 5 timing modes.
Coil Voltage	120VAC - 110VDC

Shipping and Ordering

Category	21651 - Timers, Plug-In, Type JCK (Excludes JCK60 & 70)
Discount Schedule	CP2
Article Number	785901032540
Package Quantity	1
Weight	0.24 lbs.
Availability Code	S
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.